


POWER METER III

NETWORK TESTING



Part of EXFO's 600 handheld series, which includes the FOT-600 Optical Loss Test Set and the FLS-600 Light Source, the highly versatile FPM-600 Power Meter is designed for link and system qualification. Its green/red LED indicator gives you a pass or fail test verdict according to the thresholds you have defined, for faster and easier field operation.

Thanks to its memory capacity of 1000 data items and its converter software, the FPM-600 facilitates data management and enables data transfer to a PC via USB connection.

Suited for All Network Types

The FPM-600 is a very powerful tool for the most demanding applications, such as high-speed DWDM or CWDM network qualification. With more than 40 calibrated wavelengths, it allows for user-defined measurement wavelengths, using the interpolation method between calibrated points. Use its Hold Min/Max Power function to measure system power burst or fluctuations.

FTTx Ready

EXFO's FPM-600 allows for the testing of passive optical networks (PONs) at 1310 nm, 1490 nm and 1550 nm, the three wavelengths recommended by the ITU-T (G.983.3) for PONs.

Rugged and Versatile

Like all EXFO portable instruments, the FPM-600 is built for top ruggedness and versatility, perfect for the harshest test conditions. It features a keypad/LCD backlight, for easy operation in darker environments. What's more, it is powered by a rechargeable battery.





Power Meter

SPECIFICATIONS 1

Model	FPM-602	FPM-602X	
Detector	Ge	GeX	
Power range (dBm) ²	10 to -70	26 to -55	
Wavelength range (nm)	800 to 1650	800 to 1650	
Number of calibrated wavelengths (nm)	40	40	
Power uncertainty ³	± 5 % ± 0.1 nW	\pm 5 % \pm 3 nW	
Resolution (dB)	± 0.01 (10 to -60)	± 0.01 (26 to -45)	
Automatic offset nulling ⁴	Yes	Yes	
Display units	dB, dBm, W	dB, dBm, W	
Tone detection	270 Hz, 1 kHz and 2 kH	z 270 Hz, 1 kHz and 2 kH	
Automatic wavelength recognition ⁵	Yes	Yes	
Warm-up period (min) ⁶	0	0	
Data storage (items)	more than 1000	more than 1000	
Battery life (hours) (typical)	72	72	
Warranty and recommended recalibration into	erval (years) 3	3	
VFL ⁷			
Emitter type	Laser		
Wavelength (nm)	650		
Output power (dBm)	3		
General Specifications			
Size (H x W x D) 19	.0 cm x 10.0 cm x 6.2 cm (7 1/2 in x 4 in x 2 1/2 in)	
	18 kg (1.1 lb)	

-10 °C to 50 °C

-40 °C to 70 °C

0 % to 95 % non-condensing

Connector Adapter

Standard Accessories

User guide, Certificate of Calibration, instrument stickers in six languages, AC adapter/charger, lithium ion battery, shoulder strap, hard carrying case, USB cable.

Safety

21 CFR 1040.10 and IEC 60825-1:1993+A1:1997+A2:2001: CLASS 3R LASER PRODUCT FOR VFL OPTION



Notes

- Guaranteed unless otherwise specified. All specifications valid at 1550 nm and 23 °C ± 1 °C, with an FC connector.
- 2. In CW mode; sensitivity defined as 6 x rms noise level.
- 3. For calibrated wavelengths. Valid up to 20 dBm for FPM-602X.
- 4. For power > -40 dBm for FPM-602, and > -25 dBm for FPM-602X.
- At 850 nm, 1300 nm, 1310 nm, 1490 nm, 1550 nm and 1650 nm; for power > -50 dBm for FPM-602 and > -40 dBm (typical) for FPM-602X.
- For variation ≤ 0.06 dB at 23 °C ± 1 °C; at power levels ≥ -40 dBm for FPM-602 and ≥ -25 dBm for FPM-602X.
- 7. Typical values in 62.5/125 μm fiber.

ORDERING INFORMATION

operating

storage

Temperature

Relative humidity

FPM-60X-XX-XX

(14 °F to 122 °F)

(-40 °F to 158 °F)

Model
FPM-602 = Ge detector
FPM-602X = High-power Ge detector

Example: FPM-602X-FOA-22-VFL

FOA-12 = Biconic detector FOA-14 = D4, D4/PC FOA-16 = SMA/905. \$

FOA-16 = SMA/905, SMA/906 FOA-22 = FC (PC/SPC/UPC/APC), NEC-D3

FOA-28 = DIN 47256 (LSA): DIN 47256 (PC/APC) FOA-32 = ST (PC/SPC/UPC) FOA-40 = Diamond HMS-OHFS-3 (3.5 mm) FOA-54 = SC (PC/SPC/UPC/APC) FOA-76 = FSMA HMS-10/AG, HFS-10/AG FOA-78 = Radiall EC

FOA-84 = Diamond HMS-10, HFS-13 FOA-96B = E-2000 FOA-98 = LC

FOA-99 = MU

Visual Fault Locator

00 = Without visual fault locator VFL = With visual fault locator (Universal 2.5 mm connector)

Find out more about EXFO's extensive line of high-performance portable instruments by visiting our website at www.exfo.com.



Rugged Handheld Solutions

- -OLTS
- Light source
- -Talk set



Optical Fiber

- -OTDR
- OBL motor
- ORL meter

DWDM Test Systems

- -OSA
- -- PMD analyzer
- Chromatic dispersion analyzerMultiwavelength meter

Transport/Datacom

- = 10/100 and Gigabit Ethernet
- SONET/SDH (DS0 to OC-192c)SDH/PDH (64 kb/s to STM-64c)
- _SAN

Corporate Headquarters > 400 Godin Avenue, Vanier (Quebec) G1M 2K2 CANADA | Tel.: 1 418 683-0211 | Fax: 1 418 683-2170 | info@exfo.com

		Toll-	-free: 1 800 663-3936 (USA	and Canada) www.exfo.com
EXFO America	4275 Kellway Circle, Suite 122	Addison, TX 75001 USA	Tel.: 1 800 663-3936	Fax: 1 972 836-0164
EXFO Europe	Le Dynasteur, 10/12 rue Andras Beck	92366 Meudon la Forêt Cedex FRANCE	Tel.: +33.1.40.83.85.85	Fax: +33.1.40.83.04.42
EXFO Asia-Pacific	151 Chin Swee Road, #03-29 Manhattan House	SINGAPORE 169876	Tel.: +65 6333 8241	Fax: +65 6333 8242
EXFO China	Beijing New Century Hotel Office Tower, Room 1754-1755	Beijing 100044 P. R. CHINA	Tel.: +86 (10) 6849 2738	Fax: +86 (10) 6849 2662
	No. 6 Southern Capital Gym Road			

EXFO is certified ISO 9001 and attests to the quality of these products. This device complies with Part 15 of the FCC Rules. Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. EXFO has made every effort to ensure that the information contained in this specification sheet is accurate. However, we accept no responsibility for any errors or omissions, and we reserve the right to modify design, characteristics and products at any time without obligation. Units of measurement in this document conform to SI standards and practices. Contact EXFO for prices and availability or to obtain the phone number of your local EXFO distributor.

For the most recent version of this spec sheet, please go to the EXFO website at http://www.exfo.com/specs In case of discrepancy, the Web version takes precedence over any printed literature.





